



"CREEPER 2.0" WORKSHOP STOOL

with adjustable height, rolling
incl. tooltray and 2 bottle holders
code 720669

optional (not included)

anti-slippery rubber feet, 50 mm
Set of 5 pieces
code 720679



- 1 - Compact Durable Bottom Tool Tray
- 2 - Half-Dome Rotational Hardware Tray
- 3 - 5 Wheels Reinforced Stool Base
- 4 - Adjustable Hydraulic Seating Post
- 5 - Swivel TPR/TPU Caster (5 pieces)
- 6 - Dual Layer Comfort Wide-Pan PE Seat
- 7 - Extended Cup & Bottle Holder (2 pieces)

1. Place the 5 arm stool base flipped and Insert and push 5 Wheels to the stool base securely and firmly.

2. Place the bottom tool tray on top of the stool base.

3. Insert the adjustable Hydraulic Seat Post into the stool base and make sure it sits straight nicely.

4. Insert the half-dome rotational hardware bin into the hydraulic post and make it sitting evenly on the post top shoulder.

5. Install and lock the metal bracket underside of the PE Wide Pan Seat with the hardware and washers pack.

6. Once metal bracket installed, align the wide pan PE seat and insert onto the top of the hydraulic post. Make sure the Seat metal bracket underside is tightly fit into the hydraulic post.

7. Upon complete the assembly, gently sit on the stool, move around on the even surface first so that all assembly are fit and tighten firmly before using on all surface.

8. Adjust the seating position with the underside rod accordingly.

